760243432 | PNL-CS-12SCX-RPT



LazrSPEED® Splicing cassette, OM4, 12 SC/UPC, Ribbon

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber cassette with ribbon pigtail

Product Brand LazrSPEED®

General Specifications

Adapter ColorAquaInterface, frontSC/UPC

Interface, rear Ribbon pigtail

Total Fibers, quantity 12

Total Ports, quantity, front 6

Dimensions

 Height
 28.956 mm | 1.14 in

 Width
 104.648 mm | 4.12 in

 Depth
 165.354 mm | 6.51 in

 Pigtail Length
 1.5 m | 4.921 ft

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED® 550

Insertion Loss, typical0.3 dBReturn Loss, minimum25 dB

Environmental Specifications

Safety Standard UL

COMMSCOPE®

760243432 | PNL-CS-12SCX-RPT

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
| | |

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

