

760244930 | G2-SP-24LCG-RPT



G2 Splice Cassette, 24LC/UPC with internal shutters, OS2, with ribbon pigtails

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber cassette with ribbon pigtail |
| Product Series | G2 |

General Specifications

| | |
|-------------------------------|-----|
| Interface, front | LC |
| Shuttered | Yes |
| Total Fibers, quantity | 24 |

Dimensions

| | |
|---------------|----------------------|
| Height | 1.04 in 26.416 mm |
| Width | 3.8 in 96.52 mm |
| Depth | 6.51 in 165.354 mm |

Optical Specifications

| | |
|--------------------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2 |
| Insertion Loss, maximum | 0.2 dB |

Environmental Specifications

| | |
|--------------------------------|---------------------------|
| Qualification Standards | IEC 61753-1 TIA-568.3-D |
| Safety Standard | UL |

Packaging and Weights

760244930 | G2-SP-24LCG-RPT

| | |
|---------------------------|--|
| Included | SMOUV holder SMOUV splice protection |
| Packaging quantity | 1 |
| Weight, net | 0.271 lb 0.123 kg |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

