

7712981-00

Rack 19" 47 HU 600x600 perforated

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type Network cabinet, with perforated doors

General Specifications

Color Gray
Mounting M6 Cage nut rail mounting
Note Static load rating is 1000 kg
Rack Type EIA 19 in

Dimensions

Height 2200 mm | 86.614 in
Height, guide rails 2,089.15 mm | 82.25 in
Width 600 mm | 23.622 in
Depth 600 mm | 23.622 in

Electrical Specifications

Electrical Safety Standard UL | cUL
Voltage Range On-site configuration dependant

Material Specifications

Material Type Galvanized sheet metal | Powder-coated, textured

Packaging and Weights

Height, packed 2380 mm | 93.701 in
Width, packed 760 mm | 29.921 in
Depth, packed 1222 mm | 48.11 in
Included Cables ducts (2) | Cage nuts M6 (92) | Grounding cables (10) | Grounding rail (1) | Guide rails (20) | Raised head screws M6 (92)

7712981-00

Packaging quantity	1
Weight, gross	220 kg 485.016 lb
Weight, net	115 kg 253.531 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

