

# CK9475-000 | FIST-RSKG-1



FIST Gel Sealing Kit for round splice closure port, sealing 1 cable with diameter between 11 and 14 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

## Product Classification

|                              |                 |
|------------------------------|-----------------|
| <b>Regional Availability</b> | EMEA            |
| <b>Product Type</b>          | Gel sealing kit |
| <b>Product Series</b>        | FIST-GC02       |

## General Specifications

|                                |                                       |
|--------------------------------|---------------------------------------|
| <b>Application</b>             | For use with FIST-GC02 Fiber closures |
| <b>Cable Capacity, maximum</b> | 1                                     |
| <b>Color</b>                   | Black                                 |

## Dimensions

|                                       |                  |
|---------------------------------------|------------------|
| <b>Single Cable Diameter, maximum</b> | 14 mm   0.551 in |
| <b>Single Cable Diameter, minimum</b> | 11 mm   0.433 in |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Included</b>           | Cable termination brackets   Dummy plugs   Multi-out gel seal |
| <b>Packaging quantity</b> | 1   |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>             |
|---------------|-----------------------------------|
| CHINA-ROHS    | Above maximum concentration value |
| ROHS          | Compliant/Exempted                |
| UK-ROHS       | Compliant                         |



