

CY7081-000 | FOSC-RSKG-16



FOSC™ Gel Sealing Kit for round splice closure port, sealing 16 cables with diameter up to 3 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

Regional Availability	EMEA
Product Type	Gel sealing kit
Product Brand	FOSC™
Product Series	FOSC 400G

General Specifications

Application	For use with FOSC-400G Fiber closures
Cable Capacity, maximum	16
Color	Black

Dimensions

Single Cable Diameter, maximum	3 mm 0.118 in
---------------------------------------	-----------------

Packaging and Weights

Included	Cable termination brackets Dummy plugs Multi-out gel seal
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



