FL2-96RPNL



FL2000 Fiber Termination Panel, unloaded, 96 Ports, 6RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FL2000

General Specifications

Functionality Patching

Color Putty white

Growth Configuration Unloaded

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 6

Shelf MovementHingedSplicing Capacity, maximum0

Total Ports, quantity 96

Dimensions

 Height
 266.7 mm | 10.5 in

 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Material Specifications

Finish Powder coated

Material Type Steel

COMMSCOPE®

FL2-96RPNL

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

