FL2-C280024KN-1A00



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 24 LC/UPC, singlemode, 3RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FL2000

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 2

 Cable Exit Location
 Rear, left side | Rear, right side

Color Putty white

Growth Configuration Partially loaded

Interface, front LC/UPC

Rack Type EIA 19 in

Rack Units 3

Shelf MovementHingedSplicing Capacity, maximum48

Total Ports, quantity 24

Dimensions

 Height
 133.35 mm | 5.25 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



FL2-C280024KN-1A00



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

COMMSCOPE®

FL2-C280024KN-1A00

Regulatory Compliance/Certifications

A	gency	Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

