

FPS-FMTSP-CJJ02

FMT Fiber Optic Splitter Patch Panel, 1U, 19 in, 1x16 splitter, SC/APC splitter and output connect., 2 splitters



Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	FMT

General Specifications

Device Type	Patch panel
Functionality	Splitting
Access	Front
Circuits, quantity	1
Distribution Type	1 x 16 splitter
Interface, front	SC/APC
Rack Units	1
Split Ratio	Symmetrical
Splitter, quantity	1
Total Ports, quantity	17

Dimensions

Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in
Depth	177.8 mm 7 in
Cable Stub Length	0 m 0 ft

Optical Specifications

FPS-FMTSP-CJJ02

Directivity, minimum	60 dB
Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1 dB
Wavelength Range	1260–1635 nm
Insertion Loss, Splitter, maximum	13.5 dB
Insertion Loss, Splitter, typical	13.2 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

