FPX-3FRP08-1442



FPX Fiber Optic Termination/Splice Module, 3RU, 19in, Singlemode, 144 fiber, LC/UPC Connector, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FPX

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 6

Body Style Symmetrical

Cable Exit Location Rear, left side | Rear, right side

144

ColorPutty whiteColor, frontPutty whiteGrowth ConfigurationFully loadedInterface, frontLC/UPC

Rack Type EIA 19 in | EIA 23 in

Rack Units 3

Patching Capacity, maximum

Shelf MovementSlidingTotal Fibers, quantity144Total Ports, quantity144

Dimensions

 Height
 133.35 mm | 5.25 in


 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Ordering Tree



FPX-3FRP08-1442



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Packaging and Weights

Included Mounting hardware

COMMSCOPE®

FPX-3FRP08-1442

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

