


FJWMPMPDK

Base Product



Singlemode MPO (Unpinned) to MPO (Unpinned), InstaPATCH® 360
Pre-terminated Indoor/Outdoor Trunk Cable, 72-Fiber, Low Smoke Zero
Halogen

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX InstaPATCH® 360
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Black
Color, connector A	Green
Color, boot B	Black
Color, connector B	Green
Construction Type	InstaPATCH® 360 trunk/extension/cross-connect, indoor/outdoor
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Female
Interface, Connector B	MPO-12/APC Female
Jacket Color	Black
Polarity	Method B (LL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	72


Dimensions

Cable Assembly Length Range (m)	3 – 999
--	---------

FJWMPMPDK

Cable Assembly Length Range (ft) 10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor | Outdoor

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760150615 – Fiber Indoor/Outdoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, Gel-Free,

FJWMPMPDK

Z-072-MP-8W-F12BK/D

72 fiber multi-unit with 12 fiber subunits, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color, Dca flame rating

860366137

- MPO12, LOW LOSS, FEMALE, Singlemode, GREEN, 3mm