AFGLGLGL1

Base Product



Fiber Patch Cord, Singlemode G.657.A2, Grade B, LC/APC to LC/APC, Simplex, 1.6 mm LSZH jacket

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, simplex

Product Series AFG

General Specifications

Connector A, quantity 1

Color, connector A Green

Connector B, quantity

Color, connector B Green

Interface, Connector A LC/APC

Total Fibers, quantity 1

Transmission Standards IEC 61755

Dimensions

Interface, Connector B

Cable Assembly Length Range (m) 1 - 999
Cable Assembly Length Range (ft) 1 - 999


Diameter Over Jacket 1.6 mm | 0.063 in

Ordering Tree



LC/APC

AFGLGLGL1



Mechanical Specifications

Minimum Bend Radius, loaded50 mm | 1.969 inMinimum Bend Radius, unloaded30 mm | 1.181 inTensile Load, long term, maximum33 N | 7.419 lbfTensile Load, short term, maximum110 N | 24.729 lbf

Cable Crush Resistance, maximum3.5 N/mm | 19.986 lb/in

Mating Durability, maximum 0.2 dB @ 500 cycles

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Performance Grade IEC Random Mating Grade B

Insertion Loss, maximum, connector A0.25 dBInsertion Loss, maximum, connector B0.25 dBReturn Loss, minimum, connector A65 dBReturn Loss, minimum, connector B65 dB

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Environmental Space Dual Rated LSZH/Riser

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications



AFGLGLGL1

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



Included Products

460159816 – Fiber indoor cable, Low Smoke Zero Halogen YL G.657 .A2, 1 fiber, Singlemode G.657.A2, 1.6

mm diameter, Feet jacket marking, Yellow jacket color

860637445 – LC/APC Connector, Singlemode, Green

* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

