

PTS1P-HMQR

PTS1-50-P SureFlex® Jumper with interface types 4.3-10 Male and QMA Male Right angle, Variable Length



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Cable assembly, plenum
Product Series	PTS1-50-P

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	4.3-10 Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Length	0 m 0 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.222	20.01

Jumper Assembly Sample Label

PTS1P-HMQR



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

PTS1-50-P

- PTS1-50, HELIAX[®] Superflexible High Power, High Temperature 50 Ohm Plenum Rated Coaxial Cable, corrugated copper, 1/4 in, white FR-PVC jacket.