
U4XLULUCF

Base Product



Ultra Low Loss ULL LazrSPEED® 550 LC/UPC Uniboot to LC/UPC Uniboot Ruggedized fanout Cable, 24-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

in meters | Minimum length may vary based on cable configuration

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Ruggedized fanout
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be

General Specifications

Color, boot A	Blue
Color, connector A	Black
Color, boot B	Blue
Color, connector B	Black
Construction Type	Stranded
Furcation Color	Aqua
Interface, Connector A	LC/UPC
Interface Feature, connector A	Uniboot
Interface, Connector B	LC/UPC
Interface Feature, connector B	Uniboot
Jacket Color	Aqua
Fibers per Subunit, quantity	12
Total Fibers, quantity	24
Dimensions	

Cable Assembly Length Range (m) 3 - 305

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



U4XLULUCF

Cable Assembly Length Range (ft)

10 - 999

Ordering Tree

	BASE	CODE	M [.] [.]		•	
Jac	cket Color		Breakout Length / Option	L	ength	
N	Aqua	E	24 inch breakout, no gland			
		F	24 inch breakout, with gland			
		1	33/60 inch breakout, no gland			
		2	33/60 inch breakout, with gland			
		3	33/60 inch breakout, with pulling grip	L.	UOM	
		н	48 inch breakout, no gland	F	Feet	
		J	48 inch breakout, with gland	Μ	Meter	
		-L	72 inch breakout, no gland			
		М	72 inch breakout, with gland			
		S	36 inch breakout, no gland			
		U	36 inch breakout, with gland			
		V	60 inch breakout, no gland			
		W	60 inch breakout, with pulling grip			

Optical Specifications

Fiber Mode Fiber Type Multimode

OM4, LazrSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)	
EN50575 CPR Cable EuroClass Fire Performance	B2ca	
Environmental Space	Indoor Low Smoke Zero Halogen (LSZH)	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

COMMSCOPE[®]

U4XLULUCF

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

