



RJ45 Patch Cord, category 6, yellow, 7 ft

Product Classification

| | |
|------------------------------|-------------------------|
| Regional Availability | Latin America |
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |

General Specifications

| | |
|-------------------------------|--------------------|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Stranded |
| Interface, Connector A | RJ45 plug |
| Interface, Connector B | RJ45 plug |
| Jacket Color | Yellow |
| Pairs, quantity | 4 |

Dimensions

| | |
|---|-------------------|
| Cord Length | 2.13 m 6.988 ft |
| Compatible Conductor Gauge, stranded | 24 AWG |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |

1989800-7

ROHS

Compliant

