

RG142-TNMNM-1M

RG142 Braided Jumper with interface types N Male and N Male, 1 m



Product Classification

Product Type	Braided cable assembly
Product Series	RG142

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	RG142
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
---------------	----------------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.152	23.02

Jumper Assembly Sample Label

RG142-TNMNM-1M



Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

RG142TNM-CR – Type N Male for RG142 braided cable