

# L4P43A-PDMNR-2M

---

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 N Male Right angle, 2 m



## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	LDF4-50A

## General Specifications

<b>Attachment, Connector B</b>	Field attachment
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	7-16 DIN Male
<b>Interface, Connector B</b>	N Male

## Dimensions

<b>Length</b>	2 m   6.562 ft
<b>Nominal Size</b>	1/2 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
710–806 MHz	1.2	20.83
806–960 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13
2535–2655 MHz	1.2	20.83

## Jumper Assembly Sample Label

# L4P43A-PDMNR-2M



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015  
**Classification** Designed, manufactured and/or distributed under this quality management system



## Included Products

- LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant)