

F1P43A-PSMNM-10M

FSJ1P-50A SureFlex® Jumper with interface types SMA Male and N Male, 10 m



Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	10 m 32.808 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–806 MHz	1.15	23.13
806–960 MHz	1.13	24.29
1427–1535 MHz	1.13	24.29
1700–2300 MHz	1.15	23.13
2535–2655 MHz	1.25	19.08
3400–3800 MHz	1.25	19.08

Jumper Assembly Sample Label

F1P43A-PSMNM-10M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system