

# F4A-PDMDM-2M

---

FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 2 m



## Product Classification

|                       |                     |
|-----------------------|---------------------|
| <b>Product Type</b>   | SureFlex® standard  |
| <b>Product Brand</b>  | HELIAX®   SureFlex® |
| <b>Product Series</b> | FSJ4-50B            |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Straight      |
| <b>Interface, Connector A</b>             | 7-16 DIN Male |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                |
|---------------------|----------------|
| <b>Length</b>       | 2 m   6.562 ft |
| <b>Nominal Size</b> | 1/2 in         |

## Electrical Specifications

|                         |        |
|-------------------------|--------|
| <b>DTF, Connector A</b> | -34 dB |
| <b>DTF, Connector B</b> | -34 dB |

## Jumper Assembly Sample Label

# F4A-PDMDM-2M



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

