

L4R-HMHM-6M-D



D-CLASS LDF4RK-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, with black non-halogenated fire retardant polyolefin jacket, 6 m

Product Classification

| | |
|-----------------------|--------------------------------|
| Product Type | SureFlex® D-CLASS, dynamic PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | LDF4-50A |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 6 m 19.685 ft |
| Nominal Size | 1/2 in |

Logo Image

L4R-HMHM-6M-D



Electrical Specifications

| | |
|--|----------------------|
| 3rd Order IMD Dynamic | -119 dBm |
| 3rd Order IMD Dynamic Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|-----------------------|-------------|-------------------------|
| 698–960 MHz | 1.065 | 30.04 |
| 1700–2200 MHz | 1.065 | 30.04 |
| 2200–2700 MHz | 1.083 | 27.99 |
| 3400–3800 MHz | 1.222 | 20.01 |

Jumper Assembly Sample Label

L4R-HMHM-6M-D



Environmental Specifications

| | |
|--|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |