



## i-POI™ Active Low Power Point of Interface, AWS 1700 band

### Product Classification

<b>Product Type</b>	Active point of interface, low power
<b>Product Brand</b>	i-POI™

### General Specifications

<b>BTS Interface Location, Rx/Tx combined</b>	Front
<b>DAS Interface Location, Rx from DAS</b>	Front
<b>DAS Interface, Tx to DAS</b>	QMA Female
<b>DAS Interface, Tx to DAS, Quantity</b>	2
<b>Note</b>	Test tone at all frequencies in selected DL frequency band

### Electrical Specifications

<b>Composite Output Power per DAS1 DL port</b>	16 dBm
<b>Composite Output Power per DAS2 DL port</b>	16 dBm
<b>License Band</b>	AWS 1700

### Packaging and Weights

<b>Weight, net</b>	2.7 kg   5.952 lb
--------------------	-------------------

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

