

## Tel-Splice Connector, 3-wire, dry, yellow



### **OBSOLETE**

This product was discontinued on: August 1, 2016

## Product Classification

### **Regional Availability**

Asia | EMEA | Latin America | North America

### **Product Type**

Splice

### **Product Series**

Tel-Splice

## General Specifications

### **Color**

Yellow

### **Connector Sealant**

Dry

## Dimensions

### **Compatible Insulated Conductor Diameter, maximum**

2.03 mm | 0.08 in

### **Compatible Conductor Gauge, solid**

26–19 AWG

## Material Specifications

### **Contact Plating Material**

Tin

## Environmental Specifications

### **Operating Temperature**

-40 °C to +85 °C (-40 °F to +185 °F)

### **Environmental Space**

Outdoor

## Packaging and Weights

### **Packaging quantity**

100

# 1-552678-4

---

**Packaging Type**

Box | Carton

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

