



Fiber Optic Simplex Adapter, Singlemode SC/UPC, blue, with integrated retainer

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber adapter
Product Series	OC-ADI

General Specifications

Body Style	Simplex
Color	Blue
Interface	SC/UPC
Mounting	Square flange
Total Ports, quantity	1
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Material Specifications

Alignment Sleeve Material	Ceramic
----------------------------------	---------

Mechanical Specifications

Coupling Retention Force	70 N 15.737 lbf
---------------------------------	-------------------

Optical Specifications

Fiber Mode	Singlemode
Insertion Loss, maximum	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

