



LightCrimp®, LightCrimp Plus™ Fiber Optic Termination Kit LC/SC/ST, without Microscope

OBSOLETE

This product was discontinued on: April 3, 2023

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit
Product Brand	LightCrimp Plus™ LightCrimp®
Product Series	LightCrimp

General Specifications

Interface	LC MTRJ SC ST
------------------	---------------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Included	0.3um white film 5um light gray film Alcohol fiber wipes Ball and hex key Die set, front and rear lightcrimp Fiber cleaver Instruction sheet Kevlar cutter LC+ LC/SC cable holder Miller dual-hole strip tool Polishing pad Polishing plate 8.5X11 in Pro-crimper, LC+ LC/SC/Splice Resilient polishing pad SC polishing bushing ST cable-buffer holder ST crimp die ST polishing bushing Slitter tool, 2 mm and 3 mm Strip length template Stripper, micro-strip W/.008BLA Wrench, open end ¼
-----------------	--

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

1278949-2

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



Included Products

760243578 – Fiber Optic Hand Held Precision Cleaver Tool



Fiber Optic Hand Held Precision Cleaver Tool

- Provides operator-independent precision quality cleaves in a hand held size
- Includes a blade knife with a 48,000 cleave lifetime
- Suited for field installable mechanical splice connectors, bare fiber adapters and fusion and mechanical splicing
- Supplied with a padded belt case with neck lanyard for convenience and storage

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit

Dimensions

Height	46 mm 1.811 in
Width	53 mm 2.087 in
Length	55 mm 2.165 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
Weight, net	500 g 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

