

LS2-XXXM-W-D

D-CLASS LSF2-50 SureFlex® Jumper with interface types NEX10 Male and NEX10 Male with HELIAX® SureGuard weatherproofing



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	NEX10 Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	3/8 in
---------------------	--------

Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Logo Image

LS2-XXXM-W-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-970 MHz	1.065	30
1700-2200 MHz	1.083	28
2200-2700 MHz	1.106	26
3400-3800 MHz	1.222	20
4000-6000 MHz	1.288	18

Jumper Assembly Sample Label

LS2-XXXM-W-D



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition