760005264 | M81-SVHS-110-246



S-Video to 110 Punchdown Module, ivory

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Multimedia outlet

General Specifications

ColorIvoryMountingSnap-inUTP 110 Terminal Block110 ohm

Electrical Specifications

Attenuation dc at Frequency, maximum 2 dB @ 5.5 MHz

Crosstalk @ Gain at Frequency -60 dB @ 5.5 MHz

Impedance75 ohmInsulation Resistance, minimum50 MOhm

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 °F to +140 °F) Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Relative Humidity 5%–95%, non-condensing

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications



760005264 | M81-SVHS-110-246

Agency

Classification

ISO 9001:2015





