FPX-1FSJ/02GU031



FPX Fiber Optic Termination Panel with Armored Cable, 1RU, 19in, Singlemode, 24 fiber, SC/APC connectors, Stub tail at far end, putty white, 31m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 2

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC

Color Putty white

Growth Configuration Fully loaded

Interface, front SC/APC

Interface, rear Stub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Fibers, quantity 24

Total Ports, quantity 24

Dimensions

Height 44.45 mm | 1.75 in

Width 482.6 mm | 19 in


Depth 304.8 mm | 12 in

Cable Length 31 m | 101.706 ft

COMMSC PE®

FPX-1FSJ/02GU031

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Page 2 of 3

FPX-1FSJ/02GU031

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

