

# RCP-4KBPUK11467B



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/UPC to LC/UPC breakouts, 114m cable with 67 inch breakout length and 1.2 MM Breakout Jacketing

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Regional Availability</b> | Latin America   North America       |
| <b>Portfolio</b>             | CommScope®                          |
| <b>Product Type</b>          | Fiber patch panel, with rapid cable |
| <b>Product Brand</b>         | RapidFiber®                         |
| <b>Product Series</b>        | RCP                                 |

## General Specifications

|                                  |   |
|----------------------------------|---|
| <b>Functionality</b>             | Patching                                      |
| <b>Body Style</b>                | Symmetrical                                   |
| <b>Cable Exit Location</b>       | Rear, left side                               |
| <b>Cable Stub Type</b>           | IFC, stranded                                 |
| <b>Color</b>                     | Putty white                                   |
| <b>Door Type, front</b>          | Hinged   Slide latch   Transparent            |
| <b>Growth Configuration</b>      | Fully loaded                                  |
| <b>Interface, front</b>          | LC/UPC  |
| <b>Interface, rear</b>           | LC/UPC  |
| <b>Patch Cord Entry Location</b> | Front, left side   Front, right side          |
| <b>Rack Type</b>                 | EIA 19 in   EIA 23 in                         |
| <b>Rack Units</b>                | 4   |
| <b>Shelf Movement</b>            | Sliding                                       |
| <b>Total Fibers, quantity</b>    | 288   |
| <b>Total Ports, quantity</b>     | 288   |
| <b>Transmission Standards</b>    | IEC 60794-2   ISO/IEC 11801   TIA/EIA-568-B.3 |

## Dimensions

|               |                 |
|---------------|-----------------|
| <b>Height</b> | 177.8 mm   7 in |
|---------------|-----------------|

# RCP-4KBPUK11467B

|                        |                  |
|------------------------|------------------|
| <b>Width</b>           | 482.6 mm   19 in |
| <b>Depth</b>           | 381 mm   15 in   |
| <b>Breakout Length</b> | 67 in            |

## Ordering Tree



ONLY FOR MULTIMODE VERSION.<sup>1</sup>  
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE<sup>2</sup>  
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.<sup>3</sup>  
 ONLY AVAILABLE IN LC288 4RU<sup>4</sup>

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |                       |
|-------------------|-----------------------|
| <b>Fiber Mode</b> | Singlemode            |
| <b>Fiber Type</b> | G.652.D   G.657.A2/B2 |

# RCP-4KBPUK11467B

---

## Environmental Specifications

|                                |  |
|--------------------------------|--|
| <b>Operating Temperature</b>   | -5 °C to +55 °C (+23 °F to +131 °F)  |
| <b>Storage Temperature</b>     | -40 °C to +70 °C (-40 °F to +158 °F)   |
| <b>Relative Humidity</b>       | 5%–85%, non-condensing   |
| <b>Qualification Standards</b> | NEBS Level 3   Telcordia GR-1435   Telcordia GR-326   Telcordia GR-409   UL 1863 |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Included Products

|                                |   |  |
|--------------------------------|---|--|
| 760245201<br>P-024-MP-8V-F30YL | – | Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color |
|--------------------------------|---|--|