

RCP-4ZBPUK04667B



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/APC to LC/UPC breakouts, 46m cable with 67 inch breakout length and 1.2MM Breakout Jacketing

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel, with rapid cable |
| Product Brand | RapidFiber® |
| Product Series | RCP |

General Specifications

| | |
|----------------------------------|---|
| Functionality | Patching |
| Body Style | Symmetrical |
| Cable Exit Location | Rear, left side |
| Cable Stub Type | IFC, stranded |
| Color | Putty white |
| Door Type, front | Hinged Slide latch Transparent |
| Growth Configuration | Fully loaded |
| Interface, front | LC/APC |
| Interface, rear | LC/UPC |
| Patch Cord Entry Location | Front, left side Front, right side |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 4 |
| Shelf Movement | Sliding |
| Total Fibers, quantity | 288 |
| Total Ports, quantity | 288 |
| Transmission Standards | IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3 |

Dimensions

| | |
|---------------|-----------------|
| Height | 177.8 mm 7 in |
|---------------|-----------------|

RCP-4ZBPUK04667B

| | |
|------------------------|------------------|
| Width | 482.6 mm 19 in |
| Depth | 381 mm 15 in |
| Breakout Length | 67 in |

Ordering Tree

RCP X - X X X X U X X X X X X X

| Panel Color | |
|-------------|---|
| B | Black ¹ (Leave blank for 5M) |

| Panel Size | |
|------------|----------------|
| 1 | 1U (1.75") EIA |
| 3 | 3U (5.25") EIA |
| 4 | 4U (7.00") EIA |

| Front Bulkhead Adapter/Connector | |
|----------------------------------|---------------------------|
| T | SC OM4 MULTIMODE (AQUA) |
| C | LC OM4 MULTIMODE (AQUA) |
| 7 | SC/APC SINGLEMODE SIMPLEX |
| K | LC/APC SINGLEMODE SIMPLEX |
| J | SC/APC SINGLEMODE SIMPLEX |
| Z | LC/APC SINGLEMODE SIMPLEX |

| Fiber Count of Loaded | |
|-----------------------|------------------------|
| 1 | 12 FIBER |
| 2 | 24 FIBER |
| 4 | 48 FIBER |
| 7 | 72 FIBER |
| A | 144 FIBER |
| B | 288 FIBER ² |

| Cable Construction | |
|--------------------|----------|
| U | Stranded |

| Cable Type | |
|------------|-----------------------------|
| P | INDOOR RATED (RISER/PLENUM) |
| D | INDOOR/OUTDOOR |

| Far End Connector | |
|-------------------|---------------------------|
| T | SC OM4 MULTIMODE (AQUA) |
| C | LC OM4 MULTIMODE (AQUA) |
| K | LC/APC SINGLEMODE SIMPLEX |
| J | SC/APC SINGLEMODE SIMPLEX |
| Z | LC/APC SINGLEMODE SIMPLEX |
| 7 | SC/APC SINGLEMODE SIMPLEX |

| Cable Length (in meters) ¹ | |
|---------------------------------------|------------------------------|
| 031 | 100 FT SPOOLED (31 METERS) |
| 061 | 200 FT SPOOLED (61 METERS) |
| 092 | 300 FT SPOOLED (92 METERS) |
| 122 | 400 FT SPOOLED (122 METERS) |
| 153 | 500 FT SPOOLED (153 METERS) |
| 183 | 600 FT SPOOLED (183 METERS) |
| 213 | 700 FT SPOOLED (213 METERS) |
| 244 | 800 FT SPOOLED (244 METERS) |
| 274 | 900 FT SPOOLED (274 METERS) |
| 305 | 1000 FT SPOOLED (305 METERS) |
| For Fiber Count = 288 Fiber (B) | |
| 023 | 75 FT SPOOLED (23 METERS) |
| 046 | 150 FT SPOOLED (46 METERS) |
| 069 | 225 FT SPOOLED (69 METERS) |
| 092 | 300 FT SPOOLED (92 METERS) |
| 114 | 375 FT SPOOLED (114 METERS) |
| 137 | 450 FT SPOOLED (137 METERS) |
| 160 | 525 FT SPOOLED (160 METERS) |
| 183 | 600 FT SPOOLED (183 METERS) |
| 206 | 675 FT SPOOLED (206 METERS) |
| 229 | 750 FT SPOOLED (229 METERS) |

| Breakout Jacketing | |
|--------------------|-----------------------------|
| | 2.00MM BREAKOUT |
| A | 900UM BREAKOUT |
| B | 1.2MM BREAKOUT ⁴ |

| Breakout Length | |
|-----------------|----------------------|
| 09 | 108" (9 FT BREAKOUT) |
| 25 | 25" BREAKOUT |
| 39 | 39" BREAKOUT |
| 45 | 45" BREAKOUT |
| 67 | 67" BREAKOUT |

ONLY FOR MULTIMODE VERSION.¹
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE²
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.³
 ONLY AVAILABLE IN LC288 4RU⁴

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|-----------------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.652.D G.657.A2/B2 |

RCP-4ZBPUK04667B

Environmental Specifications

| | |
|--------------------------------|--|
| Operating Temperature | -5 °C to +55 °C (+23 °F to +131 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | 5%–85%, non-condensing |
| Qualification Standards | NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863 |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Included Products

| | | |
|--------------------------------|---|--|
| 760245201 P-024-MP-8V-F30YL | – | Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color |
|--------------------------------|---|--|