IFC-7/02050-NGF

Intra Facility Fiber Cable, OS2, SC/UPC- stub, 48F, 50 m, NGF breakout 96-, 144-position

Product Classification

 Regional Availability
 Latin America | North America

 Product Type
 Fiber distribution cable assembly

Product Series IFC

General Specifications

Connector A, quantity48Color, boot ABlueColor, connector ABlueConnector B, quantity0

Construction TypeStrandedInterface, Connector ASC/UPC

Interface, Connector B Unterminated

Jacket Color Yellow

Total Fibers, quantity 48

Dimensions

Cord Length 50 m | 164.042 ft

Optical Specifications

Fiber Mode Singlemode

Fiber TypeOS2Insertion Loss, maximum, connector A0.2 dBReturn Loss, minimum, connector A55 dB

Environmental Specifications

Environmental Space Riser

Packaging and Weights

Packaging quantity 1



IFC-7/02050-NGF

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

