

IFC-K/0FJ003-2A

Intra Facility Fiber Cable, OS2, LC/UPC-stub, 3 m, FL2 breakout 12-exit up/down

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	IFC

General Specifications

Color, boot A	Blue
Color, connector A	Blue
Connector A, quantity	12
Connector B, quantity	0
Construction Type	Stranded
Interface, Connector A	LC/UPC
Interface, Connector B	Unterminated
Jacket Color	Yellow
Total Fibers, quantity	12

Dimensions

Cord Length	3 m 9.843 ft
--------------------	----------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2

Environmental Specifications

Environmental Space	Riser
----------------------------	-------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

IFC-K/0FJ003-2A

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

