

MIFC-9/02C120-NGF

Fiber Optic Intra Facility Cable, Multimode, OM2, SC/UPC to Stub, orange, 120 m

OBSOLETE

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	IFC

General Specifications

Color, boot A	Beige
Color, connector A	Beige
Connector A, quantity	48
Connector B, quantity	0
Interface, Connector A	SC/UPC
Interface, Connector B	Unterminated
Jacket Color	Orange
Total Fibers, quantity	48

Dimensions

Cord Length	120 m 393.701 ft
--------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM2

Environmental Specifications

Environmental Space	Riser
----------------------------	-------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

MIFC-9/02C120-NGF

Agency

CHINA-ROHS
REACH-SVHC
ROHS

Classification

Above maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant/Exempted

