


EH1458-002



Fiber Optic Duplex Adapter, Multimode LC/UPC, OM3/OM4, aqua, flangeless

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Fiber adapter

General Specifications

Body Style	Duplex
Color	Aqua
Interface	LC/UPC
Mounting	No flange
Shuttered	No
Total Ports, quantity	2
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Dimensions

Width	15.4 mm 0.606 in
Length	29.2 mm 1.15 in

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Multimode
Insertion Loss, maximum	0.2 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0

EH1458-002

Packaging and Weights

Included Dust caps

Packaging Type Bag

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

