

F1A-XMDM-5M-P

FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 7-16 DIN Male, 5 m



Product Classification

Product Type	SureFlex® Premium, static PIM
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	Nex10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-112 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	30
1700–2200 MHz	1.09	28
2500–2700 MHz	1.11	26
3400–3800 MHz	1.23	20

F1A-XMDM-5M-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition