260103731 | RFP-130S41LC-CS



RapidFiber® Faceplate, pull & click SC/APC, 30 meters cable on spool, cavity mount

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber wall outlet, with cable

Product Brand RapidFiber®

Product Series RFP

General Specifications

Color White

Cover Type Hinged with latches

Interface Type SC/APC

Mounting Cavity mount

Port Capacity, maximum 2

Total Ports, quantity 1

Dimensions

 Height
 74.93 mm | 2.95 in

 Width
 115.062 mm | 4.53 in

 Depth
 14.986 mm | 0.59 in

 Cable Length
 30 m | 98.425 ft

 Cable Diameter
 1 mm | 0.039 in

Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode Fiber Type G.657.B3



260103731 | RFP-130S41LC-CS

Environmental Specifications

Operating Temperature $-10 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (+14 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted

