6-555174-3 | MP-66S-LF-1



Modular Plug, 6P/6C, shielded, long body, flat oval, 2.79×6.85 mm cable jack OD, category 3, 100/bag

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio CommScope®

Product Type Modular plug

General Specifications

ANSI/TIA Category 3

Cable Type Flat oval, unshielded

Conductor Type Solid | Stranded

InterfaceRJ12Positions/Loaded Contacts6/6Termination TypeIDC

Dimensions

Compatible Cable Diameter, maximum6.85 mm0.27 inCompatible Cable Diameter, minimum2.79 mm0.11 inCompatible Insulated Conductor Diameter, maximum0.99 mm0.039 in

Compatible Insulated Conductor Diameter, minimum 0.86 mm | 0.034 in

Contact Plating Thickness 1.27 μm Compatible Conductor Gauge, solid 26–24 AWG Compatible Conductor Gauge, stranded 26–24 AWG

Electrical Specifications

 Current Rating, maximum
 0.75 A

 Insulation Resistance, minimum
 500 mOhm

Page 1 of 2

6-555174-3 | MP-66S-LF-1

Safety Voltage Rating 150 Vac

Material Specifications

Contact Base Material Phosphor Bronze

Contact Plating Material Gold

Material Type Glass filled polycarbonate

Plug Shield Base Material Copper alloy

Plug Shield Plating Material Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Relative Humidity Up to 93%, non-condensing

Safety Standard UL 1863

Packaging and Weights

Packaging quantity 100

Classification

Packaging Type Bag | Box | Carton

Regulatory Compliance/Certifications

Agency CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant **UK-ROHS** Compliant



