## 6-555176-2 | MP-66U-LF-5



Modular Plug, 6P/6C, unshielded, long body, flat oval,  $2.79 \times 6.85$  mm cable jack OD, category 3, 500/bag

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio CommScope®

**Product Type** Modular plug

General Specifications

ANSI/TIA Category 3

Cable TypeFlat oval, unshielded

Conductor Type Solid | Stranded

Interface RJ12

Positions/Loaded Contacts 6/6

Termination Type IDC

**Dimensions** 

Compatible Cable Diameter, maximum6.85 mm0.27 inCompatible Cable Diameter, minimum2.79 mm0.11 in

Compatible Insulated Conductor Diameter, maximum 0.99 mm | 0.039 in

**Compatible Insulated Conductor Diameter, minimum** 0.86 mm | 0.034 in

Contact Plating Thickness 1.27 µm

Compatible Conductor Gauge, solid 26–24 AWG

Compatible Conductor Gauge, stranded 26–24 AWG

Electrical Specifications

Current Rating, maximum 0.75 A

**Insulation Resistance, minimum** 500 m0hm

Page 1 of 2



## 6-555176-2 | MP-66U-LF-5

Safety Voltage Rating 150 Vac

Material Specifications

**Contact Base Material** Phosphor Bronze

**Contact Plating Material** Gold

**Material Type** Glass filled polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

**Environmental Specifications** 

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Safety Standard** UL 1863

Packaging and Weights

**Packaging quantity** 500

Classification

**Packaging Type** Bag | Box | Carton

Regulatory Compliance/Certifications

**Agency** CHINA-ROHS

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

**ROHS** Compliant **UK-ROHS** Compliant



**REACH-SVHC** 

