

AT-30-43-FFI6

30 dB Low PIM Attenuator 555–2700 4.3-10 F-F



OBSOLETE

This product was discontinued on: July 31, 2021

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Attenuator

General Specifications

Device Type	Attenuator
Application	Indoor/Outdoor
Color	Silver
Inner Contact Plating	Silver
Interface	4.3-10 Female
Interface 2	4.3-10 Female
Outer Contact Plating	Trimetal

Dimensions

Height	76 mm 2.992 in
Width	130 mm 5.118 in
Length	263 mm 10.354 in

Electrical Specifications

3rd Order IMD	-162 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Return Loss, minimum	19 dB

AT-30-43-FFI6

Attenuation	30 dB
Attenuation Tolerance	±1.2 dB @ 698–2700 MHz ±2.1 dB @ 555–698 MHz
Average Power, maximum	100 W
Impedance	50 ohm
Operating Frequency Band	555 – 2700 MHz
VSWR	1.25

Environmental Specifications

Operating Temperature	-25 °C to +50 °C (-13 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	150 mm 5.906 in
Width, packed	225 mm 8.858 in
Length, packed	370 mm 14.567 in
Weight, gross	3.37 kg 7.43 lb
Weight, net	2.8 kg 6.173 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

