



MMO Type Flush Mounted Angled Faceplate, four port ivory

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Flush mount outlet
<b>Product Series</b>	M Series

## General Specifications

<b>Application</b>	Has 45 degree angular ports for fiber and copper connectors
<b>Color</b>	Ivory
<b>Mounting</b>	Flush
<b>Total Ports, quantity</b>	4

## Dimensions

<b>Height</b>	144.526 mm   5.69 in
<b>Width</b>	83.312 mm   3.28 in
<b>Depth</b>	32.766 mm   1.29 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.159 kg   0.35 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

