



Rapid Fiber™ Faceplate, LC/APC, 30 meters cable on spool, wall mount

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Faceplate kit
<b>Product Brand</b>	Rapid Fiber™
<b>Product Series</b>	RFP

## General Specifications

<b>Cover Type</b>	Hinged with latches
<b>Interface Type</b>	LC/APC
<b>Mounting</b>	Wall mount
<b>Port Capacity, maximum</b>	2
<b>Total Ports, quantity</b>	1

## Dimensions

<b>Height</b>	74.93 mm   2.95 in
<b>Width</b>	115.062 mm   4.53 in
<b>Depth</b>	52.07 mm   2.05 in
<b>Cable Length</b>	30 m   98.425 ft
<b>Cable Diameter</b>	1 mm   0.039 in

## Material Specifications

<b>Material Type</b>	LSZH Thermoplastic
----------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Indoor

## Packaging and Weights

**Packaging quantity** 1