



Rapid Fiber™ Faceplate, LC/APC, 60 meters cable on spool, wall mount

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Faceplate kit
Product Brand	Rapid Fiber™
Product Series	RFP

General Specifications

Cover Type	Hinged with latches
Interface Type	LC/APC
Mounting	Wall mount
Port Capacity, maximum	2
Total Ports, quantity	1

Dimensions

Height	74.93 mm 2.95 in
Width	115.062 mm 4.53 in
Depth	52.07 mm 2.05 in
Cable Length	60 m 196.85 ft
Cable Diameter	1 mm 0.039 in

Material Specifications

Material Type	LSZH Thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1