

FGS-HNTS-12MM



FiberGuide® Top Support C-Bracket Kit, 12mm for 2x6, 4x4, 4x6in Systems

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Bracket
Bracket Type	C-bracket
Bracket Installation Type	N/A
Attachment Type	Threaded rod

Dimensions

Height	304.8 mm 12 in
Width	38.1 mm 1.5 in
Length	203.2 mm 8 in
Thread Size	12 mm
System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 51 mm x 152 mm (2 in x 6 in)

Ordering Tree

FGS-HNTS-12MM

FGS - - - - - - -

For Section Size

9	<input type="text" value="empty"/>	4 x 4 in, 4 x 6 in
	<input type="text" value="F"/>	4 x 12 in

For Threaded Rod Size

10	<input type="text" value="1/2"/>	1/2 in
	<input type="text" value="1/2-LP"/>	1/2 in, low profile
	<input type="text" value="12MM"/>	12 mm
	<input type="text" value="12MM-LP"/>	12 mm, low profile
	<input type="text" value="14MM"/>	14 mm
	<input type="text" value="14MM-LP"/>	14 mm, low profile
	<input type="text" value="16MM"/>	16 mm
	<input type="text" value="16MM-LP"/>	16 mm, low profile
	<input type="text" value="5/8"/>	5/8 in
	<input type="text" value="5/8-LP"/>	5/8 in, low profile

11	<input type="text" value="A"/>	Adjustable
----	--------------------------------	------------

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware | Locking Washers | Nuts | Quick Knobs | Screws | Washers

Packaging quantity 1

Weight, net 1.017 kg | 2.242 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

