

FGS-MIDY-125F



FiberGuide® 2" Flex Tube, Slotted, 125ft Length, Yellow

OBSOLETE

This product was discontinued on: October 1, 2023

Replaced By:

FGS-MIDY-200F

FiberGuide® 2" Flex Tube, Slotted, 200ft Length, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Convoluted tube
Product Brand	FiberGuide®
Product Series	FGS

General Specifications


Product Feature	Round Slotted
Color	Yellow
Orientation	Vertical
Section Type	Vertical section

Dimensions

Length	38100 mm 1,500.001 in
Tube Outer Diameter	50.8 mm 2 in

Ordering Tree

FGS-MIDY-125F



Tube Color

9	empty	yellow
	B	black

Tube Length, examples

11	5F	5 feet
	350F	350 feet

Tube Type

10	MIDY	Slotted flexible tube, 2 in diameter
	MFTY	Slotted flexible tube, 7/8 in diameter
	MISY	Solid flexible tube, 2 in diameter
	MLDY	Slotted flexible tube, 1 in diameter

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	9.274 kg 20.446 lb
--------------------	----------------------

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

