

FGSB-MD4E-A



FiberGuide® 45° Down Elbow, 4x4in, Black

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Elbow |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|-----------------------------|---------------|
| Angle/Bend Direction | 90° down |
| Color | Black |
| Orientation | Horizontal |
| Section Type | Elbow section |

Dimensions

| | |
|--------------------------|-------------------------------|
| System Dimensions | 102 mm x 102 mm (4 in x 4 in) |
|--------------------------|-------------------------------|

Ordering Tree



Section Color

| | | |
|---|-------|--------|
| 9 | empty | yellow |
| | B | black |

Section Size

| | | |
|----|---|-----------|
| 10 | A | 4 x 4 in |
| | B | 4 x 6 in |
| | C | 2 x 2 in* |
| | F | 4 x 12 in |
| | G | 2 x 6 in |
| | H | 4 x 24 in |

* FGS-MD4A-C or FGSB-MD4A-C

FGSB-MD4E-A

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.236 kg | 0.52 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

