



OCC1P Wideband Splitter, planar, singlemode, 1x8, symmetrical split ratio, SC/UPC, 0.9 mm cable, medium duty housing

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Splitter component
<b>Product Series</b>	OCC1P

## General Specifications

<b>Device Type</b>	Component, rectangular
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use in FOSS closures
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 8 splitter
<b>Interface, Input</b>	SC/UPC
<b>Interface, Output</b>	SC/UPC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Pigtail Length, Input</b>	1.5 m   4.921 ft
<b>Pigtail Length, Output</b>	1.5 m   4.921 ft
<b>Pigtail Diameter, Input</b>	0.9 mm   0.035 in
<b>Pigtail Diameter, Output</b>	0.9 mm   0.035 in

## Environmental Specifications

**Qualification Standards**

Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

