



Boot Assembly, 4 in

Product Classification

Product Type	Boot assembly
Product Brand	I-Line
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Color	Black

Dimensions

Height	101.6 mm 4 in
Length	76.2 mm 3 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	129.54 mm 5.1 in
Length, packed	99.06 mm 3.9 in
Included	Boot Two clamps

294573

Packaging quantity 1
Weight, gross 0.8 kg | 1.764 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

