

# 380714-000 | RPBS-C-I-25/15-100

RPBS wraparound delivery sleeve heat shrink kit, pressurized, for 15 to 25 mm cable diameter, 100 mm sheet opening



- Combines an improved application method for standard resin blocking compounds with the advantages of the wraparound heat-shrinkable sleeve
- Used with suitable commercially available resins, the system forms a pressure block for the whole pressurized cable range

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Heat shrink delivery sleeve
<b>Product Series</b>	RPBS

## General Specifications

<b>Color</b>	Black
<b>Sealant Type</b>	Hotmelt adhesive

## Dimensions

<b>Height</b>	180 mm   7.087 in
<b>Length</b>	430 mm   16.929 in
<b>Expanded Inside Diameter, minimum</b>	25 mm   0.984 in
<b>Recovered Inside Diameter, maximum</b>	15 mm   0.591 in
<b>Single Cable Diameter, maximum</b>	25 mm   0.984 in
<b>Single Cable Diameter, minimum</b>	15 mm   0.591 in

## Material Specifications

<b>Material Type</b>	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

## Environmental Specifications

# 380714-000 | RPBS-C-I-25/15-100

---

**Environmental Space** Buried | Ducted

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

