

RPBS wraparound delivery sleeve heat shrink kit, pressurized, for 50 to 70 mm cable diameter, 200 mm sheet opening



- Combines an improved application method for standard resin blocking compounds with the advantages of the wraparound heat-shrinkable sleeve
- Used with suitable commercially available resins, the system forms a pressure block for the whole pressurized cable range

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

| | |
|------------------------------|-----------------------------|
| Regional Availability | EMEA |
| Product Type | Heat shrink delivery sleeve |
| Product Series | RPBS |

General Specifications

| | |
|---------------------|------------------|
| Color | Black |
| Sealant Type | Hotmelt adhesive |

Dimensions

| | |
|---|--------------------|
| Height | 325 mm 12.795 in |
| Length | 550 mm 21.654 in |
| Expanded Inside Diameter, minimum | 70 mm 2.756 in |
| Recovered Inside Diameter, maximum | 50 mm 1.969 in |
| Single Cable Diameter, maximum | 70 mm 2.756 in |
| Single Cable Diameter, minimum | 50 mm 1.969 in |

Material Specifications

| | |
|----------------------|---|
| Material Type | Fiber-reinforced multi-layer sealing sleeve |
|----------------------|---|

Environmental Specifications

Environmental Space Buried | Ducted

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

