

611925-000 | ACBS-W-40/30

ACBS Air and water adhesive cable blocking heat shrink kit, pressurized, wrap around, for 30 to 40 mm cable diameter, 300 mm long



- Designed to be installed both vertically and horizontally
- Non-toxic components and no special tools required
- Suitable for both, new constructions and maintenance

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink repair sleeve
Product Series	ACBS

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Height	270 mm 10.63 in
Length	300 mm 11.811 in
Expanded Inside Diameter, minimum	40 mm 1.575 in
Single Cable Diameter, maximum	40 mm 1.575 in
Single Cable Diameter, minimum	30 mm 1.181 in
Expanded Wall Thickness, minimum	1.1 mm 0.043 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

Environmental Specifications

611925-000 | ACBS-W-40/30

Environmental Space Buried

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

