

# 1316MCLICK

---



Miniature Click-on Hanger for 13–16 mm cable, Hardware Sold Separately (search MCLICK-SERIES-HARDWARE for options available)

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Click-on hanger
<b>Mounting</b>	M8 through hole

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	38.1 mm   1.5 in
<b>Width</b>	24.9 mm   0.98 in
<b>Length</b>	55.1 mm   2.169 in
<b>Compatible Cable Diameter Range</b>	13–16 mm
<b>Compatible Diameter, maximum</b>	16.3 mm   0.642 in
<b>Compatible Diameter, minimum</b>	13.7 mm   0.539 in
<b>Nominal Size</b>	1/2 in   3/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

# 1316MCLICK

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 44.7 cm | 17.598 in

**Width, packed** 39.4 cm | 15.512 in

**Length, packed** 17.7 cm | 6.969 in

**Packaging quantity** 10

**Weight, gross** 0.05 kg | 0.11 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power