

Stainless Steel Hardware Kit for 1/2 in or 7/8 in Double Click-on Hangers, includes M10 bolts and hardware, 181.10 mm (7.13 in) length

Product Classification

Product Type Hardware kit

Ordering Note CommScope® non-standard product

General Specifications

Thread Size M10

Dimensions

Maximum Stack Height 3

Length 181.102 mm | 7.13 in

Nominal Size 1/2 in | 7/8 in

Material Specifications

Material Type Stainless steel

Packaging and Weights

 Height, packed
 220.98 mm | 8.7 in

 Width, packed
 114.3 mm | 4.5 in

 Length, packed
 38.1 mm | 1.5 in

Included Forty flat washers | Forty lock washers | Ten M10 threaded rods | Twenty hex nuts

Packaging quantity 10

Weight, gross 1.42 kg | 3.13 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



COMMSCOPE®

243095-3

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power